

# twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL

## pHímetro BL-BGD286

[www.twilight.mx](http://www.twilight.mx)

 / [twilightsadecv](#)

 / [twilightsadecv](#)

 / [twilightsadecv](#)

## Table pH Meter

Acidity and Alkalinity must be considered when design coating formula! Digital pH Meter can display the pH of sample directly and quickly. Low cost plus high performance offers laboratory quality control for a very economical cost.

It is Ideal for all kinds of water quality, chemical testing in the laboratory and soil/fertilizer testing. Suitable for most ASTM and ISO test procedures. Great for R&D and QC applications in chemical industries and related fields.



Ordering Information → Main Technical Parameters ↓	BGD 284	BGD 285	BGD 286
pH Range	0.00 to 14.00 pH	0.00 to 14.00 pH	0.00 to 14.00 pH
Resolution & Accuracy	± 0.05 pH	± 0.01 pH	± 0.01 pH
mV Range	0 to ± 1400 mV	0 to ± 1900 mV	0 to ± 1900 mV
Temperature Compensation	Manual (0 to 60°C)	Automatic (0 to 100°C)	Manual (0 to 60°C)
Stability	± 0.05pH/3h	± 0.01pH/3h	± 0.01pH/3h
Power	220 ± 22V, AC, 50 ± 1 Hz		

### Optional Accessories:

BGD 1171/1----Plastic combination pH electrode ( for BGD 284 & 286)

BGD 1171/2----Plastic combination pH electrode ( for BGD 285)

BGD 1172/1----Corrosion resistance glass combination pH electrode

# twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL



LLÁMANOS

+52(81) 8115-1400 / +52 (81) 8173-4300

LADA Sin Costo:  
01 800 087 43 75

E-mail:  
[ventas@twilight.mx](mailto:ventas@twilight.mx)

[www.twilight.mx](http://www.twilight.mx)



/ [twightsadecv](https://www.facebook.com/twightsadecv)



/ [twightsadecv](https://twitter.com/twightsadecv)



/ [twightsadecv](https://www.youtube.com/twightsadecv)