

twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL

Analizador de humedad Fuzhou FZ-MA100C

www.twilight.mx

 / [twilightsadecv](https://www.facebook.com/twilightsadecv)

 / [twilightsadecv](https://twitter.com/twilightsadecv)

 / [twilightsadecv](https://www.youtube.com/twilightsadecv)

Moisture Analyser From Fuzhou Precise Weighing Tech

MA系列水份仪操作简单，性能卓越，广泛适用于粮食、食品、烟草、制药、石油、化工、涂料、矿产、环保等行业物料的含水率测量。

MAseries moisture meter is user-friendly , with excellent performance , widely used to test the material's rate of water content in industries such as foodstuff、 food、 tobacco、 pharmacy、 petrol、 chemical、 coating material、 minirals、 environmental protection etc.

MA系列水份仪采用背光液晶显示屏，显示清晰易读。按键式键盘，操作简单便捷。10组测量模式存储，方便不同被测物的测量选择。

MA series moisture meter with LCD bright light display , clear and easy to read ; Panels with button , easy to operate ; With 10 test mode available ,you can set it according to the sample's material



Model	Weighing Range	Readability	Temperature	Operate Temp	pan Size	Housing Size	Heating mode
MA100A	0-100	0.01g/0.1%	45-160°C	15-35°C	φ110 mm	D*W*H 325*205* 165mm	halogen lamp
MA100B		0.005g/0.05%					
MA100C		0.001g/0.01%					

Density Meter From Fuzhou Precise Weighing Tech



- ▶ LCD背光显示，显示清晰方便；
LCD back light display , clear and easy ;
- ▶ 操作简单，直接称量，直接读取测量结果；
User friendly , directly measure , directly read the test result ;
- ▶ 高智能化，可在全量程范围内去皮、清零，超载显示；
Highly intelligent,with tare、 return to zero、 overload sign in full weighing range
- ▶ 采用纯水（可设定其它液体密度参数）中置换（悬架）法；
Use Archimedes principle to measure the density by pure water or other liquid
- ▶ 可测量固体密度（选购：浮体/颗粒套件）；
Can test solid density (optional:floating body/grains kits)
- ▶ 具有容器和直读软件，可测量任何形状的固体样品；
Can measure any shape or solid sample. Price include density sets and software
- ▶ 完全直读不需要再人工运算，节省人工运算工时；
Direct read without manual calculation to save time .
- ▶ 可改变辅助液体温度补偿系数；
Can change the temperature of reference liquid to compensate the coefficient .
- ▶ 具有RS-232C接口，可与打印机、计算机等设备连接。
With RS-232C interface , connect with printer and computer etc. easily .

Model	Weighing Range	Readability	Repeatability	Sample	pan Size	Housing Size
DM1204	120	0.0001g, 0.0001g/gcc	±0.0003g	Solid	φ60 mm	D*W*H 325*205* 305mm
DM203	200	0.001g, 0.001g/gcc	±0.002g			
DM030	300	0.001g, 0.001g/gcc	±0.002g			
DM3002	3000	0.01g, 0.01g/gcc	±0.02g		φ160 mm	

twilight

INSTRUMENTOS DE MEDICIÓN INDUSTRIAL



LLÁMANOS

+52(81) 8115-1400 / +52 (81) 8173-4300

LADA Sin Costo:
01 800 087 43 75

E-mail:
ventas@twilight.mx

www.twilight.mx